

# UP34R, Heavy Duty Parallel Clamp, Copper or Aluminum

By Burndy  
Catalog # UP34R



ACSR, 6201 & 5005: 110.8(12-7) - 397.5(18-1) COPPER OR ALUM.: 3/0 STR. - 400 GROOVE A GROOVE B.

## General

Catalog Number	UP34R
Connector Type	Spacer
Material	Aluminum Alloy
Material - Hardware	Aluminum Alloy
Plated	N
Plating Type	Unplated
UPC	781810103586

## Dimensions

Dimension - Height fraction	4-17/27 in
Dimension - Height inch	4.63 in
Dimension - Height mm	117.6 mm
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Width fraction	2-17/27 in
Dimension - Width inch	2.63 in
Dimension - Width mm	67 mm

## Conductor Related

Conductor - AAAC 5005 Size A	155.4 (7);195.7 (7);246.9 (7);312.8 (19);394.5 (19);465.4 (19)
Conductor - AAAC 5005 Size A Range	155.4 (7)-465.4 (19)
Conductor - AAAC 5005 Size B	155.4 (7);195.7 (7);246.9 (7);312.8 (19);394.5 (19);465.4 (19)
Conductor - AAAC 5005 Size B Range	155.4 (7)-465.4 (19)
Conductor - AAAC 6201 Size A	155.4 (7);195.7 (7);246.9 (7);312.8 (19);394.5 (19);465.4 (19)
Conductor - AAAC 6201 Size A Range	155.4 (7)-465.4 (19)
Conductor - AAAC 6201 Size B	155.4 (7);195.7 (7);246.9 (7);312.8 (19);394.5 (19);465.4 (19)
Conductor - AAAC 6201 Size B Range	155.4 (7)-465.4 (19)
Conductor - ACSR Cmptr Size A	110.8 (12/7) Minorca;134.6 (12/7) Leghorn;159 (12/7) Guinea;176.9 (12/7) Dotterel;190.8 (12/7) Dorking;211.3 (12/7) Cochin;203.2 (16/9) Brahma;266.8 (18/1) Waxwing;266.8 (26/7) Owl;266.8 (26/7) Partridge;300.0 (26/7)

Conductor - ACSR Str Size B	Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee 110.8 (12/7) Minorca;134.6 (12/7) Leghorn;159 (12/7) Guinea;176.9 (12/7) Dotterel;190.8 (12/7) Dorking;211.3 (12/7) Cochin;203.2 (16/9) Brahma;266.8 (18/1) Waxwing;266.8 (26/7) Owl;266.8 (26/7) Partridge;300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee
Conductor - AL Str Size A	3/0;4/0;250;266.8;300;336.4;350;3
Conductor - AL Str Size A Range	3/0-400
Conductor - AL Str Size B	3/0;4/0;250;266.8;300;336.4;350;3
Conductor - AL Str Size B Range	3/0-400
Conductor - Copper Str Size A	3/0;4/0;250;300;350;400
Conductor - Copper Str Size A Range	3/0-400
Conductor - Copper Str Size B	3/0;4/0;250;300;350;400
Conductor - Copper Str Size B Range	3/0-400

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	4
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SA..038235-01](#)
- [Specifications - UP34R](#)