

UP45R36R, Heavy Duty Parallel Clamp, Copper or Aluminum

By Burndy
Catalog # UP45R36R



ACSR, 6201 & 5005: 336.4(30-7) - 795(30-19) COPPER OR ALUM.: 397.5 - 954 GROOVE A GROOVE B.

General

Catalog Number	UP45R36R
Connector Type	Spacer
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810103807

Dimensions

Dimension - Height fraction	5-7/25 in
Dimension - Height inch	5.28 in
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4 in
Dimension - Width fraction	2-22/25 in
Dimension - Width inch	2.88 in
Dimension - Width mm	73 mm

Conductor Related

Conductor - AAAC 5005 Run	394.5 (19);465.4 (19);559.5 (19);652.4 (19);740.8 (37);927.2 (37)
Conductor - AAAC 5005 Size A	394.5 (19) kcmil;465.4 (19) kcmil;559.5 (19) kcmil;652.4 (19) kcmil;740.8 (37) kcmil;927.2 (37) kcmil
Conductor - AAAC 5005 Size A Range	394.5 (19) kcmil-927.2 (37) kcmil
Conductor - AAAC 5005 Size B	155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil;312.8 (19) kcmil;394.5 (19) kcmil;465.4 (19) kcmil;559.5 (19) kcmil
Conductor - AAAC 5005 Size B Range	155.4 (7) kcmil-559.5 (19) kcmil
Conductor - AAAC 5005 Tap	155.4 (7);195.7 (7);246.9 (7);312.8 (19);394.5 (19);465.4 (19);559.5 (19)
Conductor - AAAC 6201 Run	394.5 (19);465.4 (19);559.5 (19);652.4 (19);740.8 (37);927.2 (37)
Conductor - AAAC 6201 Size A	394.5 (19) kcmil;465.4 (19) kcmil;559.5 (19) kcmil;652.4 (19) kcmil;740.8 (37) kcmil;927.2 (37) kcmil
Conductor - AAAC 6201 Size A Range	394.5 (19) kcmil-927.2 (37) kcmil
Conductor - AAAC 6201 Size B	155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil;312.8 (19) kcmil;394.5 (19) kcmil;465.4 (19) kcmil;559.5 (19) kcmil
Conductor - AAAC 6201 Size B Range	394.5 (19) kcmil-927.2 (37) kcmil
Conductor - AAAC 6201 Tap	155.4 (7);195.7 (7);246.9 (7);312.8 (19);394.5 (19);465.4 (19);559.5 (19)
Conductor - ACSR Str Run	336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis;397.5 (30/7) Larkspur;477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7)

Conductor - AL Str Run	Hawk;477.0 (30/7) Hen;556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake
Conductor - AL Str Size A	397.5;400;450;477;500;550;556.5;600;636;652.4;650 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil
Conductor - AL Str Size A Range	397 kcmil-954 kcmil
Conductor - AL Str Size B	3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Size B Range	3/0 AWG-500 kcmil
Conductor - AL Str Tap	3/0;4/0;250;266.8;300;336.4;350;397.5;400;440;450;500;550;600;700;750;800;850;900
Conductor - Copper Str Run	400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;900 kcmil
Conductor - Copper Str Size A	400 kcmil-900 kcmil
Conductor - Copper Str Size B	3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size B Range	3/0 AWG-500 kcmil
Conductor - Copper Str Tap	3/0;4/0;250;300;350;400;450;500

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SA_038235-01](#)
- [Specifications - UP45R36R](#)