



VG4, Copper Alloy Vise Connector, 1/0 Str-#4 Sol

By Burndy
Catalog # VG4



Cu Alloy Vise Connectors, 1/0 Str - #4 Sol.

General

Catalog Number	VG4
Connector Type	Stud Connector
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	WISEIT™
UPC	781810475140

Dimensions

Bolt Size	9/16 in
Dimension - B Length fraction	1 in
Dimension - B Length inch	0.97 in
Dimension - Pad Width inch	1.15 in
Dimension - Pin Diameter inch	1.70 in

Conductor Related

Conductor - Copper Solid Run	4 - 1/0
Conductor - Copper Solid Run Range	4 - 1/0
Conductor - Copper Solid Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - Copper Solid Size Range	4 AWG-1/0 AWG
Conductor - Copper Solid Tap	4 - 1/0
Conductor - Copper Solid Tap Range	4 - 1/0
Conductor - Copper Str Run	4 - 1/0
Conductor - Copper Str Run Range	4 - 1/0
Conductor - Copper Str Tap	4 - 1/0
Conductor - Copper Str Tap Range	4 - 1/0

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	125
Minimum Pack Quantity	25

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_VG_LineArt](#)
- [Sales Drawings - 10090832](#)
- [Specifications - VG4](#)