



VP4440, V-Bolt Connector for Flex or Extra Flex Conductor

By Burndy
Catalog # [VP4440](#)



750 - 1000 KCMIL GROOVE A GROOVE B.

General

Catalog Number	VP4440
Connector Type	V-Bolt
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
UPC	781810013632

Dimensions

Dimension - Height fraction	5 in
Dimension - Height inch	5.00 in
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4.00 in
Dimension - Width fraction	3-1/4 in
Dimension - Width inch	3.19 in
Dimension - Width mm	81 mm

Conductor Related

Conductor - Copper Str Size A	750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size A Range	750 kcmil-1000 kcmil
Conductor - Copper Str Size B	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size B Range	500 kcmil-800 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Carton Quantity	3
Minimum Pack Quantity	2
Pallet Quantity	360

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_VP_PAR_CLAMP_LineArt](#)
- [Sales Drawings - 50004889](#)
- [Specifications - VP4440](#)