

Substation - Copper V Type T Connector

By Burndy
Catalog # [VTT4428](#)



V Style Connectors.

Application

Substation

General

Connector Type	T-Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Plated	N
Plating Type	Unplated
Type	Bolted Tees
UPC	621945180437
UPC 12 Digit	6219451804377

Dimensions

Dimension - Height inch	2.88 in
Dimension - L Length Overall mm	137 mm
Dimension - Length Overall inch	5.38 in
Dimension - Width inch	1.69 in
Dimension - Width mm	43 mm

Conductor Related

Conductor - Connection Combination	Cable to Cable
Conductor - Copper Solid Tap	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Tap Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Run	750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	750 kcmil-1000 kcmil
Conductor - Copper Str Tap	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	1/0 -4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - sa004362-01](#)