



Stainless Steel Non-Butting W Die, 600 kcmil CU, Index 22

By Burndy
Catalog # W36RT



Non-Butting W Die, 600 kcmil CU, Index 22.

Application

Crimping

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Catalog Number	W36RT
Color Code	Green
Crimp Force Capacity	6 ton
Die Index	22
Die Type	W Die
EU RoHS Indicator	Yes
Type	Die
UPC	781810363638
UPC 12 Digit	7818103636388

Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

Logistics

Carton Quantity	80
Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	11520

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_W1CRT1_LineArt](#)
- [Sales Drawings - 10036043](#)
- [Specifications - W36RT](#)