



# WAD4035, WEJTAP Applied In-Line Disconnect Switch

By Burndy  
Catalog # [WAD4035](#)

MAX RANGE: .522 - .609 ACSR: 4/0 (6/1), 266.8 (18/1) AAC:  
4/0, 250, 266.8 (7 STR, 19 STR), 336 COMPACT 35 kV, 200 BIL.



## General

Insulator Type	Silicon
Material	Aluminum Alloy
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810489215
UPC 12 Digit	7818104892155

## Electrical Ratings

Current Rating	900 A
----------------	-------

## Conductor Related

Conductor - AAAC 5005 Size	30.58 (7) kcmil
Conductor - AAAC 5005 Size Range	30.58 (7) kcmil
Conductor - AAAC 6201 Size	30.58 (7) kcmil
Conductor - AAAC 6201 Size Range	30.58 (7) kcmil
Conductor - ACSR Str Size	4/0 (6/1) Penquin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil
Conductor - ACSR Str Size Range	4/0 (6/1) Penquin AWG-266.8 (18/1) Waxwing kcmil
Conductor - AL Str Size	4/0 AWG;250 kcmil;266 kcmil
Conductor - AL Str Size Range	4/0 AWG-266 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AAAC C 5005-Size</li> <li>• AAAC C 6201-Size</li> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	37

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 10083326](#)



A proud member of the Hubbell Family.

