



WAD55615, WEJTAP Applied In-Line Disconnect Switch

By Burndy
Catalog # [WAD55615](#)

MAX RANGE: .846 - .883 ACSR: 477 (24/7), (26/7), (30/7), 556.5 (18/1) AAC: 556 (19 STR, 37 STR) 15 kV, 110 BIL.



General

Catalog Number	WAD55615
Insulator Type	Silicon
Material	Aluminum Alloy
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810462195
UPC 12 Digit	7818104621955

Dimensions

Dimension - B Length fraction	13-2/5 in
Dimension - B Length inch	13.4 in
Dimension - Length Overall inch	45 in

Electrical Ratings

Current Rating	900 A
----------------	-------

Conductor Related

Conductor - AAAC 5005 Size	559.5 (19) kcmil
Conductor - AAAC 5005 Size Range	559.5 (19) kcmil
Conductor - AAAC 6201 Size	559.5 (19) kcmil
Conductor - AAAC 6201 Size Range	559.5 (19) kcmil
Conductor - ACSR Str Size	477.0 (24/7) Flicker kcmil; 477.0 (26/7) Hawk kcmil; 477. (30/7) Hen kcmil
Conductor - ACSR Str Size Range	477.0 (24/7) Flicker kcmil-477. (30/7) Hen kcmil
Conductor - AL Str Size	556 kcmil
Conductor - AL Str Size Range	556 kcmil
Conductor Type	<ul style="list-style-type: none"> • AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	UI
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - WAD55615_MODEL-STEP](#)
- [3D Models - WAD55615_MODEL-IGES](#)
- [3D Models - WAD55615_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10083326](#)
- [Specifications - WAD55615](#)



A Hubbell brand