



Stainless Steel W Die, Index BG

By Burndy
Catalog # [WBG](#)

W Die, Index BG



Application

Crimping

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Construction Material - Main	Stainless Steel
Crimp Force Capacity	6 ton
Die Index	BG
Die Type	W Die
EU RoHS Indicator	Yes
Sub Brand	W-DIE
Type	W-Die for Hydraulic Crimping Tools
UPC	781810440056
UPC 12 Digit	7818104400566

Conductor Related

Crimping Ranges

Copper: #6 AWG - 4/0 AWG;
Aluminum: #6 AWG - 1/0 AWG; ACSR: #6 AWG - 1/0 AWG

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Carton Quantity	120
Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	11520

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_WDIE_Lineart](#)
[Sales Drawings - 30000157](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-WBG-SPEC-EN | REV 5/2024