



# WBS12V, Cable/Wire Bundle Strap, 12 inch Long, 19-98 Mm Bundle Dia, 100 Lb (444 N) Load Rating, Crimpable Ferrule

By Burndy  
Catalog # [WBS12V](#)

Cable/Wire Bundle Strap Type 2, 12 inch Long, 19-98 Mm Bundle Dia, 100 Lb (444 N) Load Rating.

## Application

Bundles of PV wire, Micro Inverter Trunk or AC cable

## General

Catalog Number	WBS12V
EU RoHS Indicator	Contact Manufacturer
Item Type	3B
Material	304 SS ferrule and SS wire with UV rated vinyl jacketing
Mounting Method	Crimped in the field with electrician linesman pliers or standard wire cutters
Tensile Strength	100 lb.
Trade Name	WILEY
Type	Cable Clips
UPC	621945449213
UPC 12 Digit	6219454492133

## Dimensions

Dimension - Thread Size	-
Length	12 in

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - cULus	Yes
Certified Listed	UL62275
Industry Standard(s)	UL62275
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	1000
Pallet Quantity	5000

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - Wiley Wire Management Guide](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Certifications - Certificate of Compliance, UL 62275, CSA C22.2 No. 62275](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50054219](#)
- [Specifications - WBS12V](#)
- [Video - Wiley Bundling Solutions](#)

