

WCB24PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCB24PB](#)



WEJTAP Connector , 0.650 - 0.532 (Run), 0.500 - 0.324 (Tap),
With Blue Power Booster Assembly.

General

Catalog Number	WCB24PB
Color	Blue
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810870143
UPC 12 Digit	7818108701433

Dimensions

Dimension - F Width Center to Center inch	1.89 in
Dimension - G inch	1.05 in

Conductor Related

Conductor - ACSR Str Run	4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil
--------------------------	---

Conductor - ACSR Str Run Range	4/0 (6/1) Penguin AWG-266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Tap	1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap Range	1 (6/1) Robin AWG-1/0 (6/1) Raven AWG
Conductor - AL Str Run	250 kcmil;266 kcmil;300 kcmil
Conductor - AL Str Run Range	250 kcmil-300 kcmil
Conductor - AL Str Tap	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - AL Str Tap Range	1 AWG-3/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	NC

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WCR_Lineart](#)
- [Sales Drawings - 50014998](#)
- [SDS - WEJTAP Power Booster SDS](#)
- [Specifications - WCB24PB](#)