



## WCB27, WEJTAP Connector

By Burndy  
Catalog # [WCB27](#)



Wejtap connector installed with blue booster, .532-.650 (Run), .460-.575 (Tap).

### Application

For use in tap applications using large run and tap conductor sizes

### General

Catalog Number	WCB27
Connector Type	Tap
EU RoHS Indicator	Yes
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810873304
UPC 12 Digit	7818108733044

### Dimensions

Dimension - F Width Center to Center inch	1.89 in
Dimension - G inch	1.05 in

### Conductor Related

Conductor - ACSR Str Run	4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Run Range	4/0 (6/1) Penguin AWG-266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Tap	2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penguin AWG
Conductor - ACSR Str Tap Range	2/0 (6/1) Quail AWG-4/0 (6/1) Penguin AWG
Conductor - AL Str Run	250 kcmil;266 kcmil;300 kcmil
Conductor - AL Str Run Range	250 kcmil-300 kcmil
Conductor - AL Str Tap	3/0 AWG;4/0 AWG;250 kcmil
Conductor - AL Str Tap Range	3/0 AWG-250 kcmil

### Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	25
-----------------------	----

## Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Catalogs - BURNDY Master Catalog - Section J - OH Distribution  
/ Transmission

Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR\_WCB\_Lineart

Sales Drawings - 50008861

Specifications - WCB27



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-WCB27-SPEC-EN | REV 8/2024