

WCB40, WEJTAP Connector

By Burndy
Catalog # [WCB40](#)



Wejtap connector installed with blue booster, .603-.684 (Run), .162-.204 (Tap).

General

Catalog Number	WCB40
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810873403
UPC 12 Digit	7818108734033

Dimensions

Dimension - F Width Center to Center inch	2 in
Dimension - G inch	1.1 in

Conductor Related

Conductor - ACSR Str Run	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Run Range	266.8 (18/1) Waxwing kcmil-336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG
Conductor - AL Str Run	300 kcmil;336 kcmil;350 kcmil

Conductor - AL Str Run Range	300 kcmil-350 kcmil
Conductor - AL Str Tap	8 AWG;6 AWG
Conductor - AL Str Tap Range	8 AWG-6 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WCB_Lineart](#)
- [Sales Drawings - 50008861](#)
- [Specifications - WCB40](#)