

WCB41, WEJTAP Connector

By Burndy
Catalog # [WCB41](#)



Wejtap Connector With Power Booster Assembly, 10.88 IN L, 6.88 IN W, 0.600-0.684 (Run), 0.204-0.258 (Tap), Installed With Blue Booster.

General

Catalog Number	WCB41
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810873458
UPC 12 Digit	7818108734588

Dimensions

Dimension - F Width Center to Center inch	2 in
Dimension - G inch	1.1 in

Conductor Related

Conductor - ACSR Str Run	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Run Range	266.8 (18/1) Waxwing kcmil-336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Tap	5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Tap Range	5 (6/1) Thrush AWG-4 (7/1) Swanate AWG

Conductor - AL Str Run	300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Run Range	300 kcmil-350 kcmil
Conductor - AL Str Tap	4 AWG
Conductor - AL Str Tap Range	4 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
[Customer Notices - Prop 65 Notice](#)
[Excel Files - Burndy-CPI WEJTAP Connector Selector](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_WCB_Lineart](#)
[Sales Drawings - 50008861](#)
[Specifications - WCB41](#)