




WCH2-90-15GS, Galvanized Steel 2” Cable Hanger, 90° Angle

By Burndy
Catalog # [WCH2-90-15GS](#)

Galvanized Steel Cable Hanger, Bundle Diameter: 2”, 90° Angle



Features

- Compatible with NexTracker™ U-Bolt style tracker system and similar
- Innovative design that allows for quick and easy installation
- Galvanized steel provides outstanding durability and performance in all environments
- Optimal for bi-facial panels
- Compact wire compartment secures wires up and away from hazards
- Round geometry protects cable insulation from chafing due to movement
- Recommended for outdoor use
- UL1565 Listed

Application

- PV Installations
- Designed to support cables via securement around tracker bolt

General

Catalog Number	WCH2-90-15GS
Material	Galvanized Steel
UPC	621945682481

Dimensions

Diameter	2 in
----------	------

Certifications And Compliance

Certified Listed	UL1565 Listed
Industry Standard(s)	UL 1565 Listed

Logistics

Carton Quantity	1500
-----------------	------

Product Assets

[Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Literature - Bundle Pack Cable Hangers](#)
[Sales Drawings - 50127834](#)
[Sell Sheets - Wiley Wire Cable Hangers](#)
[Specifications - WCH2-90-15GS](#)