



WCY110, WEJTAP Connector

By Burndy
Catalog # [WCY110](#)



Aluminum Overhead Wedge Tap Connector, 1.302 Dia. To 1.242 Dia. (Run), 0.877 Dia. To 0.777 Dia. (Tap).

General

Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810211113
UPC 12 Digit	7818102111133

Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	2.04 in

Conductor Related

Conductor - ACSR Str Run	1033.5 (54/7) Curlew;1113 (54/19) Finch;1272 (54/19) Pheasant
Conductor - ACSR Str Run Range	1033.5 (54/7) Curlew-1272 (54/19) Pheasant
Conductor - ACSR Str Tap	397.5 (24/7) Brant;397.5 (26/7) Ibis;397.5 (30/7) Larkspur;477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen
Conductor - ACSR Str Tap Range	397.5 (24/7) Brant-477.0 (30/7) Hen
Conductor - AL Str Run	1100;1113;1192.5;1200;1272.2;1300
Conductor - AL Str Run Range	1100-1300
Conductor - AL Str Tap	450;477;500;550;556.5
Conductor - AL Str Tap Range	450-556.5

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50014998](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-WCY110-SPEC-EN | REV 1/2024