

WCY125, WEJTAP Connector

By Burndy
Catalog # [WCY125](#)



Aluminum Overhead Wedge Tap Connector, 1.422 Dia. To 1.314 Dia. (Run), 1.113 Dia. To 1.019 Dia. (Tap).

General

Catalog Number	WCY125
Color	Yellow
Connector Type	Tap
Material	Aluminum
UPC	781810094877
UPC 12 Digit	7818100948777

Dimensions

Dimension - F Width Center to Center inch	3.50 in
Dimension - G inch	2.06 in

Conductor Related

Conductor - ACSR Str Run	1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Run Range	1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Tap	636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil;715.5 (54/7) Crow kcmil;715.5 (24/7) Stilt kcmil;715.5 (26/7) Starling kcmil;715.5 (30/19) Redwing kcmil;795 (54/7) Condor kcmil;795 (26/7) Drake kcmil

Conductor - ACSR Str Tap Range	636 (30/19) Egret kcmil-795 (26/7) Drake kcmil
Conductor - AL Str Run	1300 kcmil;1351 kcmil;1400 kcmil;1431 kcmil;1500 kcmil
Conductor - AL Str Run Range	1300 kcmil-1500 kcmil
Conductor - AL Str Tap	900 kcmil
Conductor - AL Str Tap Range	900 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - WCY125](#)