

WCY140, WEJTAP Connector

By Burndy
Catalog # WCY140



Aluminum Overhead Wedge Tap Connector, 1.533 Dia. To 1.471 Dia. (Run), 1.547 Dia. To 1.471 Dia. (Tap).

General

Catalog Number	WCY140
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810231937
UPC 12 Digit	7818102319377

Dimensions

Dimension - F Width Center to Center inch	3.75 in
---	---------

Conductor Related

Conductor - ACSR Str Run	1431 (54/19) Plover kcmil;1510.5 (45/7) Nuthatch kcmil;1590 (45/7) Lapwing kcmil;1590 (54/19) Falcon kcmil
Conductor - ACSR Str Run Range	1431 (54/19) Plover kcmil-1590 (54/19) Falcon kcmil
Conductor - ACSR Str Tap	1431 (54/19) Plover kcmil;1510.5 (45/7) Nuthatch kcmil;1590 (45/7) Lapwing kcmil;1590 (54/19) Falcon kcmil
Conductor - ACSR Str Tap Range	1431 (54/19) Plover kcmil-1590 (54/19) Falcon kcmil

Conductor - AL Str Run	1600 kcmil;1700 kcmil;1750 kcmil;1800 kcmil
Conductor - AL Str Run Range	1600 kcmil-1800 kcmil
Conductor - AL Str Tap	1600 kcmil;1700 kcmil;1750 kcmil;1800 kcmil
Conductor - AL Str Tap Range	1600 kcmil-1800 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	250
-----------------------	-----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50008861](#)
- [Specifications - WCY140](#)