

WCY56, WEJTAP Connector

By Burndy
Catalog # [WCY56](#)



WEJTAP Assembly, 0.75-0.54(Run), 0.75-0.52(Tap).

Features

WEJTAP Connector installed with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

General

Catalog Number	WCY56
Connector Type	Tap
EU RoHS Indicator	Yes
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810874202
UPC 12 Digit	7818108742022

Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.37 in

Conductor Related

Conductor - ACSR Str Run	4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7)
--------------------------	--

Conductor - ACSR Str Run Range	4/0 (6/1) Penguin AWG-397.5 (26/7) Ibis kcmil
Conductor - ACSR Str Tap	4/0 (6/1) Penguin AWG-397.5 (26/7) Ibis kcmil
	4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil
Conductor - ACSR Str Tap Range	4/0 (6/1) Penguin AWG-397.5 (24/7) Brant kcmil
Conductor - AL Str Run	4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil
Conductor - AL Str Run Range	4/0 AWG-450 kcmil
Conductor - AL Str Tap	4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil
Conductor - AL Str Tap Range	4/0 AWG-450 kcmil
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus No
Certified Listed TAA Compliant (All status valid till December 2024)

Standards - RoHS Compliance Status CM
UL Listed No

Logistics

Minimum Pack Quantity 10

Product Assets

[3D Models - WCY56_MODEL-IGES](#)
[3D Models - WCY56_MODEL-PDF](#)
[3D Models - WCY56_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
[Customer Notices - Prop 65 Notice](#)
[Excel Files - Burndy-CPI WEJTAP Connector Selector](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_WCY_Lineart](#)
[Sales Drawings - 50008861](#)
[Specifications - WCY56](#)



A Hubbell brand