

WCY57, WEJTAP Connector

By Burndy
Catalog # [WCY57](#)



Wejtap Assembly , Installed With Yellow Booster, Sum of diameters: 1.190 (Max), .979 (Min).

Application

For use in tap applications using large run and tap conductor sizes

General

Connector Type	Tap
EU RoHS Indicator	Yes
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810874257
UPC 12 Digit	7818108742577

Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.53 in

Conductor Related

Conductor - ACSR Str Run	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis;397.5 (30/7) Larkspur;477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen;556.5 (24/7) Parakeet
Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich-556.5 (24/7) Parakeet
Conductor - ACSR Str Tap	4 (7/1) Swanate;3 (6/1) Swallow;2 (6/1) Sparrow;2 (7/1) Sparate;1 (6/1) Robin
Conductor - ACSR Str Tap Range	4 (7/1) Swanate-1 (6/1) Robin
Conductor - AL Str Run	336.4;350;397.5;400;450;477;500;550;556.
Conductor - AL Str Run Range	336.4-600
Conductor - AL Str Tap	4;3;2;1
Conductor - AL Str Tap Range	4-1
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_WCY_Lineart](#)
- [Sales Drawings - 50008861](#)

