

WCY59, WEJTAP Connector

By Burndy
Catalog # WCY59



Wejtap Connector With Power Booster Assembly, 12.63 IN L, 6.38 IN W, 0.666-0.893 (Run), 0.162-0.199(Tap), Installed With Yellow Booster.

Application

For use in tap applications using large run and tap conductor sizes

General

Catalog Number	WCY59
Connector Type	Tap
EU RoHS Indicator	Yes
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810874356
UPC 12 Digit	7818108743566

Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.53 in

Conductor Related

Conductor - ACSR Str Run	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis;397.5 (30/7) Larkspur;477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen;556.5 (24/7) Parakeet
Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich-556.5 (24/7) Parakeet
Conductor - ACSR Str Tap	6 (6/1) Turkey

Conductor - ACSR Str Tap Range	6 (6/1) Turkey
Conductor - AL Str Run	336.4;350;397.5;400;450;477;500;51
Conductor - AL Str Run Range	336.4-600
Conductor - AL Str Tap	6;4
Conductor - AL Str Tap Range	6-4
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WCY_Lineart](#)
- [Sales Drawings - 50008861](#)
- [Specifications - WCY59](#)