

WCY63PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY63PB](#)



Wejtap connector installed with Yellow booster, .683-.940 (Run), .481-.750 (Tap).

Features

WEJTAP Connector, packaged with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

General

Catalog Number	WCY63PB
Color	Yellow
Connector Type	Tap
EU RoHS Indicator	No
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector with Booster
UPC	781810870570
UPC 12 Digit	7818108705700

Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.53 in

Conductor Related

Conductor - ACSR Str Run	336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil;477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil;500.0 (30/7) Heron kcmil;556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Run Range	336.4 (18/1) Merlin kcmil-556.5 (30/7) Eagle kcmil

Conductor - ACSR Str Tap	2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil
Conductor - ACSR Str Tap Range	2/0 (6/1) Quail AWG-397.5 (24/7) Brant kcmil
Conductor - AL Str Run	350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil
Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Tap	3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil
Conductor - AL Str Tap Range	3/0 AWG-450 kcmil
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Standards - RoHS Compliance Status	NC

Logistics

Minimum Pack Quantity 10

Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Catalogs - BURNDY Master Catalog - Section J - OH Distribution
/ Transmission

Customer Notices - Prop 65 Notice
Excel Files - Burndy-CPI WEJTAP Connector Selector
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) -
BUR_WEJTAP_POWER_LUG_LineArt
Sales Drawings - 50014998
SDS - WEJTAP Power Booster SDS
Specifications - WCY63PB



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-WCY63PB-SPEC-EN | REV 1/2025