

WCY70, WEJTAP Connector

By Burndy
Catalog # [WCY70](#)



Wejtap Assembly, 0.940-0.683 (Run), 0.204-0.162 (Tap),
Installed With yellow Booster.

General

Catalog Number	WCY70
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810874905
UPC 12 Digit	7818108749055

Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.53 in

Conductor Related

Conductor - ACSR Str Run	300.0 (26/7) Ostrich kcmil; 336.4 (18/1) Merlin kcmil; 336.4 (26/7) Linnet kcmil; 336.4 (30/7) Oriole kcmil; 397.5 (18/1) Chickadee kcmil; 397.5 (24/7) Brant kcmil; 397.5 (26/7) Ibis kcmil; 397.5 (30/7) Larkspur kcmil; 477.0 (18/1) Pelican kcmil; 477.0 (24/7) Flicker kcmil; 477.0 (26/7) Hawk kcmil; 477. (30/7) Hen kcmil; 500.0 (30/7) Heron kcmil; 556.5 (24/7) Parakeet kcmil; 556.5 (26/7) Dove kcmil; 556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich kcmil- 556.5 (30/7) Eagle kcmil

Conductor - ACSR Str Tap	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-5 (6/1) Thrush AWG
Conductor - AL Str Run	350 kcmil;397 kcmil;400 kcmil; 450 kcmil;477 kcmil;500 kcmil; 550 kcmil;556 kcmil;600 kcmil; 636 kcmil;650 kcmil;700 kcmil
Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Tap	8 AWG;6 AWG;4 AWG
Conductor - AL Str Tap Range	8 AWG-4 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_WCY_Lineart](#)
[Sales Drawings - 50008861](#)
[Specifications - WCY70](#)