

WCY70PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY70PB](#)



WEJTAP Connector, 0.940 - 0.683 (Run), 0.204 - 0.162 (Tap),
With Yellow Power Booster Assembly.

General

Catalog Number	WCY70PB
Color	Yellow
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810870648
UPC 12 Digit	7818108706488

Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.53 in

Conductor Related

Conductor - ACSR Str Run	300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil;477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil;500.0 (30/7) Heron kcmil;556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich kcmil-556.5 (30/7) Eagle kcmil

Conductor - ACSR Str Tap	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-5 (6/1) Thrush AWG
Conductor - AL Str Run	350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil
Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Tap	8 AWG;6 AWG;4 AWG
Conductor - AL Str Tap Range	8 AWG-4 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	NC

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WEJTAP_POWER_LUG_LineArt](#)
- [Sales Drawings - 50014998](#)
- [SDS - WEJTAP Power Booster SDS](#)
- [Specifications - WCY70PB](#)