



# WCY76, WEJTAP Connector

By Burndy  
Catalog # [WCY76](#)



Wejtap Assembly , Installed With Yellow Booster, Sum of diameters: 1.901 (Max), 1.741 (Min).

## Application

For use in tap applications using large run and tap conductor sizes

## General

Connector Type	Tap
EU RoHS Indicator	Yes
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810875209
UPC 12 Digit	7818108752099

## Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.9 in

## Conductor Related

Conductor - ACSR Str Run	477.0 (30/7) Hen;556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Tap	336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis;397.5 (30/7) Larkspur;477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen;556.5 (24/7) Parakeet
Conductor - ACSR Str Tap Range	336.4 (18/1) Merlin-556.5 (24/7) Parakeet
Conductor - AL Str Run	556.5;600;636;650;700;715.5;750;795.5;800
Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Tap	350;397.5;400;450;477;500;550;556.5;600
Conductor - AL Str Tap Range	350-650
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Run</li> <li>• AL C Str-Run</li> <li>• ACSR C Str-Tap</li> <li>• AL C Str-Tap</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	5
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-WCY76-SPEC-EN | REV 5/2024