

WCY90, WEJTAP Connector

By Burndy
Catalog # [WCY90](#)

WEJTAP Connector, 1.250 - 0.893 (Run), 1.159 - 0.868 (Tap),
Installed With Yellow Booster.



General

Catalog Number	WCY90
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810875902
UPC 12 Digit	7818108759022

Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.97 in

Conductor Related

Conductor - ACSR Str Run	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil;605 (24/7) Peacock kcmil;605 (26/7) Squab kcmil;605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil;636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil;715.5 (54/7) Crow kcmil;715.5 (24/7) Stilt kcmil;715.5 (26/7) Starling kcmil;715.5 (30/19) Redwing kcmil;795 (54/7) Condor kcmil;795 (26/7) Drake kcmil;795 (30/19) Mallard kcmil;874.5 (54/7) Crane kcmil;900 (54/7) Canary kcmil;954 (45/7) Rail kcmil;954 (54/7) Cardinal kcmil;1033.5 (45/7) Ortolan kcmil;1033.5 (54/7) Curlew kcmil
Conductor - ACSR Str Run Range	556.5 (24/7) Parakeet kcmil-1033.5 (54/7) Curlew kcmil
Conductor - ACSR Str Tap	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil;605 (24/7) Peacock

kcmil;605 (26/7) Squab	kcmil;605 (30/19) Teal
kcmil;636 (24/7) Rook	kcmil;636 (26/7) Grosbeak
kcmil;636 (30/19) Egret	kcmil;666.6 (24/7) Flamingo
kcmil;715.5 (54/7) Crow	kcmil;715.5 (24/7) Stilt
kcmil;715.5 (26/7) Starling	kcmil;715.5 (30/19) Redwing
kcmil;795 (54/7) Condor	kcmil;795 (26/7) Drake
kcmil;795 (30/19) Mallard	kcmil;874.5 (54/7) Crane
kcmil;900 (54/7) Canary	kcmil;954 (45/7) Rail kcmil;954 (54/7) Cardinal kcmil;1033.5 (45/7) Ortolan kcmil;1033.5 (54/7) Curlew kcmil;1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil;1272 (54/19) Pheasant kcmil;1351.5 (54/19) Martin kcmil;1431 (54/19) Plover kcmil;1510.5 (45/7) Nuthatch kcmil;1590 (45/7) Lapwing kcmil;1590 (54/19) Falcon kcmil
Conductor - ACSR Str Tap Range	556.5 (24/7) Parakeet kcmil-1590 (54/19) Falcon kcmil
Conductor - AL Str Run	600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Run Range	600 kcmil-1000 kcmil
Conductor - AL Str Tap	650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Tap Range	650 kcmil-1000 kcmil

Conductor - ACSR Str Tap Range

Conductor - AL Str Run Range
Conductor - AL Str Tap

Conductor - AL Str Tap Range

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity 5

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_WCY_Lineart](#)

[Sales Drawings - 50008861](#)

[Specifications - WCY90](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-WCY90-SPEC-EN | REV 10/2024