



# WCY91, WEJTAP Connector

By Burndy  
Catalog # [WCY91](#)



Wejtap Assembly, 1.250-0.893 (Run), 1.130-0.856 (Tap),  
Installed With yellow Booster.

### General

Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810875957
UPC 12 Digit	7818108759577

### Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.97 in

### Conductor Related

Conductor - ACSR Str Run 556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard;874.5 (54/7) Crane;900 (54/7) Canary;954 (54/7) Cardinal;1033.5 (54/7) Curlew

Conductor - ACSR Str Run Range 556.5 (24/7) Parakeet-1033.5 (54/7) Curlew

Conductor - ACSR Str Tap 477.0 (26/7) Hawk;477.0 (30/7) Hen;556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard;874.5 (54/7) Crane;900 (54/7) Canary;954 (54/7) Cardinal;1033.5 (54/7) Curlew;1113 (54/19) Finch

Conductor - ACSR Str Tap Range 477.0 (26/7) Hawk-1113 (54/19) Finch

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_WCY\\_Lineart](#)  
[Sales Drawings - 50008861](#)

Range (34/15) 1 inch  
Conductor - AL Str Run 600;636;650;700;715.5;750;795.5;800;874.5;900;954;1000  
Conductor - AL Str Run Range 600-1000  
Conductor - AL Str Tap 556.5;600;636;650;700;715.5;750;795.5;800;874.5;900  
Conductor - AL Str Tap Range 556.5-900  
Conductor Type

- ACSR C Str-Run
- AL C Str-Run
- ACSR C Str-Tap
- AL C Str-Tap



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-WCY91-SPEC-EN | REV 5/2024