

WCY99, WEJTAP Connector

By Burndy
Catalog # [WCY99](#)



WEJTAP Connector, 1.250 - 0.893 (Run), 0.398 - 0.324 (Tap),
Installed With Yellow Booster.

General

Catalog Number	WCY99
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810876350
UPC 12 Digit	7818108763500

Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.96 in

Conductor Related

Conductor - ACSR Str Run	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil;605 (24/7) Peacock kcmil;605 (26/7) Squab kcmil;605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil;636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil;715.5 (54/7) Crow kcmil;715.5 (24/7) Stilt kcmil;715.5 (26/7) Starling kcmil;715.5 (30/19) Redwing kcmil;795 (54/7) Condor kcmil;795 (26/7) Drake kcmil;795 (30/19) Mallard kcmil;874.5 (54/7) Crane kcmil;900 (54/7) Canary kcmil;954 (45/7) Rail kcmil;954 (54/7) Cardinal kcmil;1033.5 (45/7) Ortolan kcmil;1033.5 (54/7) Curlew kcmil
--------------------------	---

Conductor - ACSR Str Run Range	556.5 (24/7) Parakeet kcmil-1033.5 (54/7) Curlew kcmil
Conductor - ACSR Str Tap	2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap Range	2 (7/1) Sparate AWG-1/0 (6/1) Raven AWG
Conductor - AL Str Run	600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Run Range	600 kcmil-1000 kcmil
Conductor - AL Str Tap	1 AWG;1/0 AWG
Conductor - AL Str Tap Range	1 AWG-1/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_WCY_Lineart](#)
[Sales Drawings - 50008861](#)
[Specifications - WCY99](#)