



## Stainless Steel W Die Kit for Copper Connectors #8 AWG-500 kcmil (12 Sets). Color coded for crimping YA and YS types of connectors

By Burndy  
Catalog # [WDIEKITCU](#)

W Die Kit for CU, #8 AWG-500 kcmil (12 Sets), for YA and YS.



### Application

Crimping

### General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Catalog Number	WDIEKITCU
Crimp Force Capacity	6 ton
Die Type	W Die
Tool Type	Die Kit, Copper
Type	Die
UPC	781810667798
UPC 12 Digit	7818106677988

### Dimensions

Dimensions	5.50 in x 8.00 in x 4.70 in
Height	4.7 in
Length	5.5 in
Width	8 in

### Conductor Related

Crimping Ranges                      Copper: #8 AWG - 500 Kcmil

### Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

### Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	462

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50040571](#)  
[Specifications - WDIEKITCU](#)