



Stainless Steel W Die Kit for Copper Connectors #8 AWG-500 kcmil (12 Sets). Color coded for crimping YA and YS types of connectors

By Burndy
Catalog # [WDIEKITCU](#)



W Die Kit for CU, #8 AWG-500 kcmil (12 Sets), for YA and YS.

Application

Crimping

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Catalog Number	WDIEKITCU
Crimp Force Capacity	6 ton
Die Type	W Die
Tool Type	Die Kit, Copper
Type	Die
UPC	781810667798
UPC 12 Digit	7818106677988

Dimensions

Dimensions	5.50 in x 8.00 in x 4.70 in
Height	4.7 in
Length	5.5 in
Width	8 in

Conductor Related

Crimping Ranges	Copper: #8 AWG - 500 Kcmil
-----------------	----------------------------

Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	462

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50040571](#)
- [Specifications - WDIEKITCU](#)