



# WEEB-DSK14, .94" WEEB disk washer, Bottom Mount Application, 0.26" hole size

By Burndy  
Catalog # [WEEB-DSK14](#)



WEEB® Washer Electrical Equipment Bond.

## Features

- Made from corrosion resistant 304 stainless steel for outstanding durability and performance
- Eliminates the need for surface preparation and oxide inhibitor
- Detailed manual specifying proper hardware, torque, and mounting information is available upon request
- UL467 Recognized for grounding and bonding equipment
- Custom grounding and bonding solutions available upon request

## Application

WEEB washers offer a simple, low cost method to bond any non-conductive coated surfaces together reducing time, labor costs and the amount of copper wiring. WEEB's patented teeth pierce through most non-conductive coatings and embed into the underlying metal creating a bonding connection between the mounting surface and coated metal component that it is installed on or between.

## General

Item Type	3B
Material	304 Stainless Steel
UPC	781810644676
UPC 12 Digit	7818106446766

## Dimensions

Dimension - Inside Diameter inch	6.75 in
Dimension - Outside Diameter inch	23.96 in
Dimension - Pad Width inch	24.11 in
Dimension - Thread Size	-

## Certifications and Compliance

Certification - CSA Approved	N
Certification - ETL	Y
Certification - UL Recognized	Y
Certification - cULus	N
Certified Listed	UL2703 Recognized
Industry Standard(s)	UL2703 Recognized
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	6000
Pallet Quantity	100

## Product Assets

[Brochures - WEEB Washer Guide and WEEB Washer Theory](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50017070](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-WEEB-DSK14-SPEC-EN | REV 1/2024