




WEEB-SSR, WEEB Top Clamp Washer, 1.70 IN L, 1.35 IN W , 0.37 IN hole size, Rigid

By Burndy
Catalog # [WEEB-SSR](#)



304 Stainless Steel Electrical Equipment Bond Washer; 1.70" Length; 1.35" Width; 0.27" Height; .37" Hole; Rigid.

Features

- Made from corrosion resistant 304 stainless steel for outstanding durability and performance
- Eliminates the need for surface preparation and oxide inhibitor
- Detailed manual specifying proper hardware, torque, and mounting information is available upon request
- UL467 Recognized for grounding and bonding equipment
- Custom grounding and bonding solutions available upon request

General

Item Type	4D
Material	304 Stainless Steel
UPC	781810537664
UPC 12 Digit	7818105376644

Dimensions

Dimension - Thread Size -

Certifications and Compliance

Certification - CSA Approved	N
Certification - ETL	Y
Certification - UL Recognized	Y
Certification - cULus	N
Certified Listed	UL467 Recognized
Industry Standard(s)	UL467 Recognized
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6000
-----------------	------

Product Assets

- [Brochures - WEEB Washer Guide and WEEB Washer Theory](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50001974](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-WEEB-SSR-SPEC-EN | REV 1/2024