



WILEYBRAID6-38, Cu Braid, 38.00 IN L, 0.87 IN W, M10 or 3/8" Hardware NOT included



By Burndy
Catalog # [WILEYBRAID6-38](#)

WILEY Bonding Jumpers are perfect for tracker applications, galvanized steel, or anywhere a WEEB® washer is not required.

Features

Perfect for tracker applications, galvanized steel or anywhere a WEEB washer is not required

Application

The corrosion resistant, tin plated copper Wiley line of bonding jumpers are high quality solutions for your system to create an electrical bond between two pieces of galvanized or other uncoated electrically conductive metals. Standard lengths range from 6" to 36", with or without installation hardware assembled or unassembled. Custom lengths are also available on request. UL467 and UL2703 Listed.

General

| | |
|----------------|----------------|
| Catalog Number | WILEYBRAID6-38 |
| Item Type | 3C |
| UPC | 621945448339 |
| UPC 12 Digit | 6219454483399 |

Dimensions

| | |
|----------------------------|--------|
| Bolt Size | 3/8 in |
| Dimension - Length Overall | 6 in |
| inch | |

Dimension - Thread Size -

Certifications And Compliance

| | |
|----------------------|--------|
| Certified Listed | UL2703 |
| Industry Standard(s) | UL2703 |
| UL Listed | Yes |

Logistics

| | |
|-----------------|-------|
| Carton Quantity | 100 |
| Pallet Quantity | 10500 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13](#)
- [Certifications - UL Certificate of Compliance, UL 2703](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50060880](#)
- [Specifications - WILEYBRAID6-38](#)