

## Stainless Steel W Die, Index K840

By Burndy  
Catalog # [WK840](#)

W Die, Index K840.



### Application

Crimping

### General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Catalog Number	WK840
Construction Material - Main	Stainless Steel
Crimp Force Capacity	6 ton
Die Index	K840
Die Type	W Die
EU RoHS Indicator	Yes
Sub Brand	W-DIE
Type	W-Die for Hydraulic Crimping Tools (set)
UPC	781810440162
UPC 12 Digit	7818104401622

### Conductor Related

### Crimping Ranges

Aluminum: 2/0 AWG- 4/0 AWG; ACSR: 2/0 AWG- 4/0 AWG

### Certifications And Compliance

Buy American Compliant	Yes
Standards - RoHS Compliance Status	EX

### Logistics

Carton Quantity	80
Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	11520

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_WDIE\\_Lineart](#)  
[Sales Drawings - 30001787](#)  
[Specifications - WK840](#)