



## Stainless Steel W Die, Index O

By Burndy  
Catalog # [WO](#)

W Die, Index O.



### Application

Crimping

### General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Construction Material - Main	Stainless Steel
Crimp Force Capacity	6 ton
Die Index	O
Die Type	W Die
EU RoHS Indicator	Yes
Sub Brand	W-DIE
Type	W-Die for Hydraulic Crimping Tools (set)
UPC	781810440452
UPC 12 Digit	7818104404522

### Conductor Related

Crimping Ranges	Copper: 14 Sol. - 350 kcmil; AAC: 14 Sol. - 3/0 AWG; ACSR: #2 AWG - 3/0 AWG
-----------------	---

### Certifications And Compliance

Standards - RoHS Compliance EX  
Status

### Logistics

Carton Quantity	80
Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	11520

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_WDIE\\_Lineart](#)  
[Sales Drawings - 50007852](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-WO-SPEC-EN | REV 5/2024