



## WTS24, Wiley Twist Strap, 24", 300 Stainless Steel Wire Core Coated with UV-Resistant PVC

By Burndy  
Catalog # WTS24



Wiley Twist Straps provide a quick, dependable wire management solution, round design protects cable insulation from damage. Corrosion-resistant 300 series stainless steel wire core coated with UV-resistant PVC. No tools required for installation. Reusable and repositionable. Tensile strength up to 40 lbs. Available in sizes 8" to 36", custom lengths available, contact customer service or your local sales representative.

### Features

- Long-lasting, labor-saving wire management solution
- Round design protects cable insulation from damage
- No tools necessary for installation or removal
- Reusable and Repositionable
- Tensile strength up to 40 lbs
- Standard sizes range from 8" to 36"
- Custom lengths available
- UL62275 Pending

### Application

Secures wires anywhere on PV system, including around torque tube

### General

Catalog Number	WTS24
Color	Black
Material	Corrosion-Resistant 300 series stainless steel wire core, coated

UPC with UV-Resistant PVC  
621945674455

### Dimensions

Length 24"

### Logistics

Carton Quantity 1000

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog Literature - Wiley Twist Strap Introduction](#)
- [Specifications - WTS24](#)
- [Video - Wiley Bundling Solutions](#)