



WTS24, Wiley Twist Strap, 24", 300 Stainless Steel Wire Core Coated with UV-Resistant PVC

By Burndy
Catalog # [WTS24](#)



Wiley Twist Straps provide a quick, dependable wire management solution, round design protects cable insulation from damage. Corrosion-resistant 300 series stainless steel wire core coated with UV-resistant PVC. No tools required for installation. Reusable and repositionable. Tensile strength up to 40 lbs. Available in sizes 8" to 36", custom lengths available, contact customer service or your local sales representative.

Features

- Long-lasting, labor-saving wire management solution
- Round design protects cable insulation from damage
- No tools necessary for installation or removal
- Reusable and Repositionable
- Tensile strength up to 40 lbs
- Standard sizes range from 8" to 36"
- Custom lengths available
- UL62275 Pending

Application

Secures wires anywhere on PV system, including around torque tube

General

| | |
|----------------|--|
| Catalog Number | WTS24 |
| Color | Black |
| Material | Corrosion-Resistant 300 series stainless steel wire core, coated |

UPC [with UV-Resistant PVC](#)
621945674455

Dimensions

Length 24"

Logistics

Carton Quantity 1000

Product Assets

- [Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Wiley Twist Strap Introduction](#)
- [Sell Sheets - Wiley Tie Strap](#)
- [Specifications - WTS24](#)
- [Video - Wiley Bundling Solutions](#)