



# Stainless Steel Nest and Indenter X-Die, OH25 Profile, Use in OUR840 POPPER™ HYTOOL™

By Burndy  
Catalog # XOH25



Nest and Indenter X-Die, OH25 Profile.

## Application

Crimping

## General

Application - For Use On	Use with OUR840 Crimper
Catalog Number	XOH25
Crimp Force Capacity	6 ton
Die Type	X Die
Type	Die
UPC	781810011157
UPC 12 Digit	7818100111577

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Package Contents	Die only

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_XNMG\\_LineArt](#)
- [Sales Drawings - 50016265](#)
- [Specifications - XOH25](#)



A Hubbell brand