



Plier-style Crimper/Cutter, Installs #22 AWG - #10 AWG Bare and Nylon Insulated Connectors; Cuts Aluminum and Copper

By Burndy
Catalog # [Y10D](#)

Plier-style Crimper/Cutter for #22-10 AWG Bare and Nylon Connectors; Cuts CU/AL.



Application

- Crimping and Cutting

General

Application - For Use On	#22-10 AWG Insulated and Uninsulated Terminals and Splices
Construction Material - Main	Steel Alloy
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Plier Hand-held Tool
Trade Name	HYTOOL™
Type	<ul style="list-style-type: none">• Crimper and Cutter• Crimper and Cutter
UPC	781810700860

Dimensions

Length	9.75 in
--------	---------

Conductor Related

Crimping Ranges	Copper: #22 AWG - #10 AWG
-----------------	---------------------------

Certifications And Compliance

Standards - RoHS Compliance	EX
Status	

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Burndy Tooling Full Catalog](#)
[Installation Manuals - BUR_476021_SOMI_Y10D and Y1022](#)
[Sales Drawings - sd211531-01](#)
[Video - Small Terminal Tools\(Y10 & MRE\)](#)



A proud member of the Hubbell Family.