



Plier-style Crimper/Cutter, Installs #22 AWG - #10 AWG Bare and Nylon Insulated Connectors; Cuts Aluminum and Copper

By Burndy
Catalog # Y10D

Plier-style Crimper/Cutter for #22-10 AWG Bare and Nylon Connectors; Cuts CU/AL.



Features

- One tool for both nylon insulated and bare connectors
- Precision machined wire cutter for aluminum and copper
- Heavy duty forged steel, rust resistant finish

Application

Crimping and Cutting

General

Application - For Use On	#22-10 AWG Insulated and Uninsulated Terminals and Splices
Construction Material - Main	Steel Alloy
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Plier Hand-held Tool
Trade Name	HYTOOL™
Type	<ul style="list-style-type: none"> • Crimper and Cutter • Crimper and Cutter
UPC	781810700860

Dimensions

Length 9.75 in

Conductor Related

Crimping Ranges Copper: #22 AWG - #10 AWG

Certifications and Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity 1
Package Contents Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Installation Manuals - BUR_476021_SOMI_Y10D and Y1022](#)
[Sales Drawings - sd211531-01](#)
[Video - Small Terminal Tools\(Y10 & MRE\)](#)



A proud member of the Hubbell Family.