



# Ergonomic Full Cycle Ratchet Hand Crimper, #12 AWG - #2 AWG Copper Stranded, Solid and Flex Wire, For use with Copper Terminals, Splices and C-Taps



By Burndy  
Catalog # [Y122CMR](#)

Ergonomic Full Cycle Ratchet Hand Crimper, #12 AWG - #2 AWG Copper.

## Features

- Overmolded comfort grip handles
- Easy groove identification with color coded dies
- UL Listed/CSA Certified connections when used with recommended BURNDY terminals/splices
- Die index embossment for all 6 wire ranges
- Emergency release mechanism in case of misalignment or mistaken die choice
- Two different kits are also available with a selection of connectors in a sturdy metal carrying case (Y122CMRKIT and Y122CMRCIKIT)

## Application

Crimping

## General

Application - For Use On	#12-2 AWG Copper Terminals and Splices and #14-4 AWG Thin-Wall C-Taps
Catalog Number	Y122CMR
Die Type	Rotating Die Wheel
EU RoHS Indicator	No
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810659694
UPC 12 Digit	7818106596944

## Dimensions

Dimensions	10.38 in x 0.75 in x 3.00 in
Height	3 in
Length	10.38 in
Weight	1.3 lb
Width	0.75 in

## Conductor Related

Crimping Ranges	Copper: #12 AWG - #2 AWG Stranded, Solid and Flex
-----------------	---

## Certifications And Compliance

Buy American Compliant	No
Standards - RoHS Compliance Status	UI

## Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR\\_50030110\\_SOMI\\_Y122CMR](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50030115](#)
- [Specifications - Y122CMR](#)
- [Video - Y122CMR Ratcheting Full Cycle Crimper](#)