



Rotating Die, Full Cycle Ratchet Hand Crimper for #8 AWG - #1 AWG Copper terminals and splices, #14 - #4 AWG Copper Thin-wall C-Taps

By Burndy
Catalog # Y1MRTC



Rotating Die, Full Cycle Ratchet Hand Crimper for #8 AWG - #1 AWG Copper terminals and splices, #14 - #4 AWG Copper Thin-wall C-Taps

Features

- Rotating die is color coded to match color coded connectors
- Molded comfort grips reduce fatigue during continuous use
- Ratchet mechanism assures a complete crimp every time

Application

Crimping

General

Application - For Use On	#8-1 AWG Copper Terminals and Splices and #14-4 AWG Thin-Wall C-Taps
Die Type	Rotating Die Wheel
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810271292

Dimensions

Dimensions	10.00 in x 3.00 in x 0.75 in
Height	0.75 in
Length	10.00 in
Width	3.00 in

Conductor Related

Crimping Ranges Copper: #8 AWG - #1 AWG

Certifications and Compliance

Standards - RoHS Compliance CM Status

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Installation Manuals - BUR_26002125_SOMI_Y1MRTC](#)
[Sales Drawings - SD213730-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-Y1MRTC-SPEC-EN | REV 1/2024