

## Y282CR, Compression Splice Reducer, Barrel A 4/0 AWG, Barrel B #2 AWG

By Burndy  
Catalog # Y282CR



4/0 AWG CU Long Barrel Size Reduced Down To 2 AWG Wire Size, Internal Chamfer, Tin Plated, Up to 35kV, PURPLE Color Code, 15 Die Index.

### Features

Copper reducing sleeve that allows a larger terminal or splice to accommodate a smaller wire gauge

### Application

Wire Reducing Splice Adapter Insert

### General

Catalog Number	Y282CR
Color Code	Purple
Connector Type	LONG BARREL
Die Index	15
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin Plated
Sub Brand	REDUCER/ADAPTER
Temperature Rating	194
Type	Y-R, Compression
UPC	781810000984
UPC 12 Digit	7818100009844

### Dimensions

Dimension - B Length inch	1.75 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	0.534 in

### Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

### Conductor Related

Conductor - Copper Str Run	4/0 AWG
Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Str Tap	2 AWG
Conductor - Copper Str Tap Range	2 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Wire Size	#2 AWG

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	24500

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SD..016040-01](#)



A Hubbell brand