



## Y284CR, Compression Splice Reducer, Barrel A 4/0 AWG, Barrel B #4 AWG

By Burndy  
Catalog # Y284CR



4/0 AWG CU Long Barrel Size Reduced Down To 4 AWG Wire Size, Internal Chamfer, Tin Plated, Up to 35kV, PURPLE Color Code, 15 Die Index.

### Features

Copper reducing sleeve that allows a larger terminal or splice to accommodate a smaller wire gauge

### Application

Wire Reducing Splice Adapter Insert

### General

Catalog Number	Y284CR
Color Code	Purple
Connector Type	LONG BARREL
Die Index	15
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
UPC	781810000991
UPC 12 Digit	7818100009911

### Dimensions

Dimension - B Length inch	1.75 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	0.534 in

### Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

### Conductor Related

Conductor - Copper Str Run	4/0 AWG
Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Copper Str Tap	4 AWG
Conductor - Copper Str Tap Range	4 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Wire Size	#4 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	100
Minimum Pack Quantity	25
Pallet Quantity	19600

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SD..016040-01](#)



A Hubbell brand