



## Y3025R, Compression Splice Reducer, Barrel A 300 kcmil, Barrel B 1/0 AWG

By Burndy  
Catalog # Y3025R



300 kcmil CU Long Barrel Size Reduced Down To 1/0 AWG Wire Size, Internal Chamfer, Tin Plated, Up to 35kV, WHITE Color Code, 17 or 298 Die Index.

### Features

Copper reducing sleeve that allows a larger terminal or splice to accommodate a smaller wire gauge

### Application

Wire Reducing Splice Adapter Insert

### General

Catalog Number	Y3025R
Color Code	White
Connector Type	LONG BARREL
Die Index	17
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
UPC	781810121405
UPC 12 Digit	7818101214055

### Dimensions

Dimension - B Length inch	2.00 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in
Dimension - Outside Diameter inch	0.637 in

### Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

### Conductor Related

Conductor - Copper Str Run	300 kcmil
Conductor - Copper Str Run Range	300 kcmil
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Copper Str Tap	1/0 AWG
Conductor - Copper Str Tap Range	1/0
Conductor - Material	COPPER
Conductor Type	CODE
Wire Size	#1/0 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	50
Minimum Pack Quantity	50
Pallet Quantity	17400

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SD..016040-01](#)



A Hubbell brand