

Y3028R, Compression Splice Reducer, Barrel A 300 kcmil, Barrel B 4/0 AWG



By Burndy
Catalog # Y3028R

300 kcmil CU Long Barrel Size Reduced Down To 4/0 AWG Wire Size, Internal Chamfer, Tin Plated, Up to 35kV, WHITE Color Code, 17 or 298 Die Index.

Features

Copper reducing sleeve that allows a larger terminal or splice to accommodate a smaller wire gauge

Application

Wire Reducing Splice Adapter Insert

General

Catalog Number	Y3028R
Color Code	White
Connector Type	LONG BARREL
Die Index	17
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
UPC	781810085172
UPC 12 Digit	7818100851722

Dimensions

Dimension - B Length inch	2.00 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in
Dimension - Outside Diameter inch	0.637 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	300 kcmil
Conductor - Copper Str Run Range	300 kcmil
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Tap	4/0 AWG
Conductor - Copper Str Tap Range	4/0 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Wire Size	#4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	29600

Product Assets

- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD..016040-01](#)
- [Specifications - Y3028R](#)