

# Y3126R, Compression Splice Reducer, Barrel A 350 kcmil, Barrel B 2/0 AWG



By Burndy  
Catalog # Y3126R

350 kcmil CU Long Barrel Size Reduced Down To 2/0 AWG Wire Size, Internal Chamfer, Tin Plated, Up to 35kV, RED Color Code, 18 or 324 Die Index.

## Features

Copper reducing sleeve that allows a larger terminal or splice to accommodate a smaller wire gauge

## Application

Wire Reducing Splice Adapter Insert

## General

Catalog Number	Y3126R
Color Code	Red
Connector Type	LONG BARREL
Die Index	18
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
UPC	781810102374
UPC 12 Digit	7818101023744

## Dimensions

Dimension - B Length inch	2.00 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in
Dimension - Outside Diameter inch	0.687 in

## Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper Str Run	350 kcmil
Conductor - Copper Str Run Range	350 kcmil
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Str Tap Range	2/0 AWG
Conductor - Copper Str Tap Range	2/0 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Wire Size	#2/0 AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	75
Minimum Pack Quantity	20
Pallet Quantity	13050

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD..016040-01](#)
- [Specifications - Y3126R](#)