



9-Ton Remote C-Head Crimper, For Navy and Commercial Cable, Rubber Covered

By Burndy
Catalog # Y34BH



9T Remote C-Head Crimper, For Navy and Commercial Cable, Rubber Covered.

Features

- Molded rubber covering
- Heavy duty return spring
- Operates on standard 10,000 psi pumps
- Lightweight design
- Molded rubber boot for body and hydraulic coupler
- Compact "C" shaped forged head
- Accommodates "B" style dies

Application

Crimping

General

Application - For Use On	Copper, Welding, N40-N500 Navy, Flexible and Extra Flexible, Aircraft Cable
Catalog Number	Y34BH
Crimp Force Capacity	9 ton
Die Type	B Die
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810408544
UPC 12 Digit	7818104085444

Dimensions

Dimensions	16.75 in x 3.00 in x 3.00 in
Height	3 in
Jaw Width	1.10 in
Length	16.75 in
Weight	8 lb
Width	3 in

Conductor Related

Crimping Ranges	Copper #4 - 500 kcmil code cable, Welding Cable: 350 kcmil, N40 to N500 Navy Cable, Flexible and Extra Flexible #4 - 4/0 Aircraft Cable; HYCRAB™ BURNDY® Network Connector System-Copper: #4 - 500 kcmil str., Aluminum: #6 - 300 kcmil
-----------------	---

Certifications And Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Metal Case

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_082_OVPF_Y34BH_lineart](#)
- [Sales Drawings - 201515](#)
- [Specifications - Y34BH](#)