



12-Ton C-Head Crimper, Self Contained Hydraulic, Uses U Dies, #8 AWG - 750 kcmil Copper and Aluminum, up to 3/4" Ground Rod

By Burndy
Catalog # Y35

12T C-Head Crimper, #8 AWG - 750 kcmil CU/AL, up to 3/4" Ground Rod.



Features

- Comfort grip handles
- Trigger controlled ram release
- Short handle throw
- Rubber covered handles
- 180° head rotation
- C-shaped head
- Hole for lifting eye
- Positive push button die locks
- Rubber body covering
- Built-in automatic 10,000 psi "Blow-Off" pressure release valve
- Rapid ram advance handle
- Y35-2 has rubber covered head

Application

Crimping

General

Application - For Use On	Copper, N30-N500 Navy, Flex: #8-750 kcmil; Aluminum: #8-750 kcmil; Grounding Taps: Copper #8-500 kcmil; Ground Rod: up to 3/4"
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimper
UPC	781810408407
UPC 12 Digit	7818104084077

Dimensions

Dimensions	23.25 in x 2.75 in x 4.75 in
Height	4.75 in
Length	23.25 in
Weight	13.5 lb
Width	2.75 in

Conductor Related

Crimping Ranges	Copper: #8 str. - 500 kcmil code cable; Copper: #8 str. - 500 kcmil and up to 3/4" ground rod; Copper: #8 str. - 750 kcmil code cable, N30 - N500 Navy cable, flexible, and extra flex; Splices to 400 kcmil only; Aluminum: #8 str. - 750 kcmil code cable
-----------------	---

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, Metal Case

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_Y35_Lineart](#)
[Sales Drawings - SD..032005-01](#)



A proud member of the Hubbell Family.