



**12-Ton Remote C-Head Crimper,  
10,000 psi, Uses U Dies, #8 AWG -  
750 kcmil Copper and Aluminum,  
up to 3/4" Ground Rod**

By Burndy  
Catalog # [Y35BH](#)



12T Remote C-Head Crimper, 10,000 psi, Uses U Dies, #8 AWG  
- 750 kcmil CU/AL, up to 3/4" Ground Rod.

**Features**

- Lifting eye
- 0.95" jaw opening
- Uses U style dies
- Positive die lock buttons

**Application**

Crimping

**General**

Application - For Use On	Copper, Aluminum, ACSR, HYGROUND® Compression Grounding, Ground Rod
Crimp Force Capacity	12 ton
Die Type	U Die
EU RoHS Indicator	Yes
Sub Brand	HYPRESS
Tool Type	Remote Hydraulic Crimper
Trade Name	HYPRESS™
UPC	781810408452
UPC 12 Digit	7818104084522

**Dimensions**

Dimension - Length Overall inch	9.75 in
Dimensions	2.62 in x 4.75 in x 9.25 in
Height	9.25 in
Jaw Width	0.95 in
Length	2.62 in
Weight	8 lb
Width	4.75 in

**Conductor Related**

Crimping Ranges

Copper #8 str. - 500 kcmil code cable (Grounding Terminals, Grounding Splices); Copper #8 str. - 500 kcmil and up to 3/4" ground rod (Grounding Taps); Copper #8 str. - 750 kcmil code cable, N30 - N500 Navy cable, flexible, and extra flex (Terminals (Bare), Terminals (Insulated), Splices to 400 kcmil only; Aluminum #8 str. - 750 kcmil code cable (Terminals, Splices to 350 kcmil only)

**Certifications And Compliance**

Standards - RoHS Compliance EX  
Status

**Logistics**

Minimum Pack Quantity	1
Package Contents	Tool, Metal Case

**Product Assets**

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_Y35BH\\_LinaArt](#)  
[Sales Drawings - SE209028-01](#)



A proud member of the Hubbell Family.